

PIERCAN USA INC.

Your Glove Containment Expert

How to Order Isolator and Short Gloves

Required Information:

True Isolator Glove:

Step 1	Step 2	Step 3	Step 4	Step 5	Step 6
Choose Port Size	Choose Material	Choose Thickness	Choose Length	Choose Hand Size	Choose Hand Style
4	Y, B, ESDB, UY, U, USY, USU, EWC UY	15, 20, 24 MIL	13	5-10	AMBI
4	ESDN, N	15, 20, 24 MIL	13	5-10	AMBI

Short Gloves for Soft Containment, Isolator Systems, and Industrial Application:

Step 1	Step 2	Step 3	Step 4	Step 5	Step 6
Choose Cuff Size	Choose Material	Choose Thickness	Choose Length	Choose Hand Size	Choose Hand Style
5	Y, B, UY, U, USY, USU	7-30 MIL	12-21	10	L/R

Anti C:

Step 1	Step 2	Step 3	Step 4	Step 5
Choose Material	Choose Thickness	Choose Length	Choose Hand Size	Choose Hand Style
ACNitrile	11 MIL	15	7-11	L/R

New: The UNIVERSAL GLOVE: Applicable for all Markets

Step 1	Step 2	Step 3	Step 4	Step 5	Step 6
Choose Cuff Size	Choose Material	Choose Thickness	Choose Length	Choose Hand Size	Choose Hand Style
4 or 5	Y, B, UY, U, USY, USU, EWC UY	7-30 MIL	12-15	U	AMBI, L/R

*Universal Hand Size (U) fits most hand size (8-11)

1. Choose Port Size: Choose from a 4 or 5" port size. **Not all port sizes are available for all materials.** (See Product Sheets per Material. <http://piercanusa.com/gloves/glovesandsleeves.html>)
2. Choose Glove Material:

Y = CSM (Chlorosulfonated Polyethylene)	N = Neoprene
B = Butyl	USY = Polyurethane/Shielding/CSM
ESD B = Electro-Static Dissipated Butyl	USU = CSM/Shielding/CSM
UY = Polyurethane/CSM	EWC UY = Extreme Wet Conditions Polyurethane/CSM
U = Polyurethane	R = Natural Rubber

3. Choose Glove Thickness in Millimeters: Standard Thicknesses: 15 mm, 20 mm, and 30 mm. Choose from 15 mm, 20mm, 24mm, and 30 mm
4. Choose Glove Length: (Measurement from the tip of the middle finger to the outer edge of the beading.) Standard Lengths: 13". Choose from 12-21".
5. Choose Hand Size: (Measured as a line from the thumb crotch to the outer of the palm.) Choose from 5- 10.5" or our Universal (One Size Fits Most) (See <http://piercanusa.com/images/measure-your-hand-size.pdf> or http://piercanusa.com/images/hand_sizing_pictorial.pdf)
6. Choose Hand Style: Choose from Left/Right or Ambidextrous hand styles. If ordering the Left/Right hand style, leave hand style blank. (Example: 10B1532-9.75)

Example: 4UY1513-8.5A (4" port size, Polyurethane/CSM, 15 mm thickness, 13" length, 8.5" hand size, Ambidextrous)