

# PIERCAN USA INC.

Your Glove Containment Expert

## How to Order Isolator, Glovebox, and Containment Gloves

### Required Information:

Step 1	Step 2	Step 3	Step 4	Step 5	Step 6
Choose Port Size	Choose Material	Choose Thickness	Choose Length	Choose Hand Size	Choose Hand Style
5, 6, 7, 8, 10, 12	Y, B, ESD B, UY, U, USY, USU, EWC UY	12, 15, 20, 24, 30 MIL	30, 32, 34	8.5, 9.75, 10.5, U	AMBI, L/R
5, 6, 7, 8, 10, 12	ESDN, N, R	12, 15, 20, 24, 30 MIL	30, 32, 34	6, 7, 8, 9, 10	AMBI, L/R

1. Choose Port Size: Choose from a 5", 6", 7", 8", 10" or 12" port size. **Not all port sizes are available for all materials.** (See Product Sheets per Material. <http://piercanusa.com/gloves/glovesandsleeves.html> )
2. Choose Glove Material:

Y = CSM (Chlorosulfonated Polyethylene)	N = Neoprene
B = Butyl	USY = Polyurethane/Shielding/CSM
ESD B = Electro-Static Dissipated Butyl	USU = CSM/Shielding/CSM
UY = Polyurethane/CSM	EWC UY = Extreme Wet Conditions Polyurethane/CSM
U = Polyurethane	

3. Choose Glove Thickness in Millimeters: Standard Thicknesses: 15 mm, 20 mm, and 30 mm. Choose from 15 mm, 20mm, 24mm, and 30 mm
4. Choose Glove Length: (Measurement from the tip of the middle finger to the outer edge of the beading.) Standard Lengths: 32". Choose from 30", 32", and 34"
5. Choose Hand Size: (Measured as a line from the thumb crotch to the outer of the palm.) Choose from 8.5", 9.75", 10.5" or our Universal (One Size Fits Most) (See <http://piercanusa.com/images/measure-your-hand-size.pdf> or [http://piercanusa.com/images/hand\\_sizing\\_pictorial.pdf](http://piercanusa.com/images/hand_sizing_pictorial.pdf))
6. Choose Hand Style: Choose from Left/Right or Ambidextrous hand styles. If ordering the Left/Right hand style, leave hand style blank. (Example: 10B1532-9.75)

Example: 6Y1532-8.5A (6" port size, CSM, 15 mm thickness, 32" length, 8.5" hand size, Ambidextrous)